

FEATURES & SPECIFICATIONS

INTENDED USE

For use with housings L5 and L5R.

CONSTRUCTION

Antique bronze, oil-rubbed bronze, brushed nickel and white finishes are one-piece aluminum open reflectors.

25° vertical tilt standard.

350° horizontal rotation.

INSTALLATION

Socket to trim interface.

Retaining clips pull and snap onto top of reflector to hold trim inside housing.

LISTINGS

U.L. Listed to U.S. and Canadian safety standards.

Damp location listed.

WARRANTY

1-year limited warranty. Complete warranty terms located at www.acuitybrands.com/CustomerResources/Terms and conditions.aspx

Actual performance may differ as a result of end-user environment and application.

 $Note: Specifications \, subject \, to \, change \, without \, notice.$



5" Finishing Trim



5E1

STANDARD EYEBALL

Narrow Flange




Height: 4 (7.6)

Lamp opening: 3-7/8 (9.8)

Diameter: 6-3/8 (16.2)

All dimensions are inches (centimeters) unless otherwise indicated.



ORDERING INFORMATION

For shortest lead times, configure product using **bolded options**.

Example: 5E1

Finish	
(blank)	Black baffle
MW	Matte white
BN	Brushed nickel
BZA	Antique bronze
ORB	Oil-rubbed bronze
W	White
(E	i blank) MW BN BZA DRB

Housing Compatibility: Housing and trim ordered separately.				
Application	Source	Maximum wattage	Housing	
		50 PAR20	L5, L5R	
IC	Incandescent	75 PAR30 long neck		
		65 BR30		
		50 R20		

Accessories: Order as separate catalog number.

CRTS 5" goof ring, white

DOWNLIGHTING 5E1

5E1 5" Standard Eyeball Full Reflector Trim

 $For BR \ and \ PAR \ reflector \ lamps, see lamp \ manufacturer's \ published \ raw \ lamp \ data \ for \ photometrics.$