



FM120-LED

12" LED FLUSHMOUNT - AZURE SERIES

Product codes

FM120-20W-3K-WH : WHITE - 3K

FM120-20W-4K-WH : WHITE - 4K

The AZURE series of LED flush mount fixtures by NDR offers an affordable and stylish design that will compliment a varied assortment of lighting applications.

Integrated LEDs are direct-AC with no external driver. The diffuser has a unique stylish design and may be removed easily for installation and cleaning. It features a quick and easy installation on a standard 3" or 4" junction box.

Available in a 12" or 16" version. Mounting hardware included.

The unit is certified ETL and Energy Star, as well as carrying a damp location rating.

It is fully dimmable and offers 50,000 hours of life. It is also available in 2 color temperatures: 3K and 4K.

Données techniques

Diameter	11.75" (298.5 mm)
Height	3.375" (85.7 mm)
Color Temperature	3K / 4K
Light Output - Lumen	1500LM
Operating Temperature	-20°C + 50°C
Dimmable	Y
CRI	80+
Voltage	120V
Watt	20W
Warranty (Years)	5

