# **STANPRO**

# **RMPS**

# **PLASTIC RUNNING MAN**

120/277/347VAC

The RMPS series is suitable for property management and institutional applications, and is designed using durable and lightweight high impact thermoplastic. Available in AC only, AC & DC, and self-powered versions.

#### **FEATURES AND SPECIFICATIONS**

#### • Electrical circuitry - AC & AC/DC

- LED ultra bright light source
- Transformer driven sign
- 120/277/347VAC Input, field selectable
- Power consumption:

120V = 0.032A/2.1W; 277V = 0.008A/1.5W; 347V = 0.012A/2.0W

Power consumption in Emergency mode:6VDC = 0.9W 12VDC = 0.8W 24VDC = 1.2W

#### • Electrical self-powered

- LED ultra bright light source
- 90 or 120 minutes emergency duration
- 120/277/347VAC Input, field selectable
- Power consumption:
   120V = 0.030A/2.70W; 277V = 0.010A/2.18W;
   347V = 0.012A/2.64W
- High-performance Ni-Cad battery





Comes standard with three pictogram legends for direction selection.





For double face no arrow options, select "0" on the options column.

#### Mechanical

- High impact, UV stabilized, thermoplastic construction
- Well suited for damp locations
- White colour is standard
- Universal mounting: ceiling mount; wall mount, end mount

#### Approvals

- CSA Certified to C22.2 #141-15
- CSA Certified to C860-11
















#### **OVERVIEW**

LED	
120/277/347VAC	
120V = 0.032A/2.1W;	
277V = 0.008A/1.5W;	
347V = 0.012A/2.0W	
120V = 0.030A/2.70W;	
277V = 0.010A/2.18W;	
347V = 0.012A/2.64W	
6VDC = 0.9W	
12VDC = 0.8W	
24VDC = 1.2W	
Transformer driven	





## **DIMENSIONS**



## **ORDERING GUIDE**

RMPS		WH -	-	
Series	Nbr of faces* and mounting	Colour	DC Output	Options
RMPS	<ul><li>0 - Universal</li><li>1 - Single face*</li><li>2 - Double face*</li></ul>	WH - White	UDC - Universal DC backup voltage from 6 to 24VDC  IB - Self-powered for 90 minutes  IB1 - Self-powered for 120 minutes	O - No indicators (double face only)  ・ ・ ・ ・ ・ ・ ・ ・ ・ ・ ・ ・ ・ ・ ・ ・ ・ ・ ・

QUICK SHIP: Not all products are Quick Ship. To view our Quick Ship qualified products, please consult our Quick Ship Product Guide at stanprols.com/quick-ship-product-guide. Product availability is subject to change without notice. Please contact your Stanpro customer service representative to confirm inventory levels at time of order.

# Comments



All products are subject to change or may be discontinued any time without notice.

 $<sup>^{\</sup>star}$  Unit comes standard as universal face. Single face or double face should only be specified when choosing nonstandard fibers.