CXST-2L/CXST12-2L

EXIT STEEL COMBO "WAY2GO"

CXST-2L

6VDC 36W Battery Capacity (Over 4 hours Duration Standalone Unit) 2 x 2W Crisp White LED Heads

CXST12-2L

12VDC 72W Battery Capacity (Over 8 hours Duration Standalone Unit) 2 x 2.5W Crisp White LED Heads



Approvals:

CSA Certified to C22.2 #141.15, C860

Energie verifie

DESCRIPTION

The commercial CXST-2L/CXST12-2L features a slim profile that prevents light leaks. Easy to install design, available in 6VDC 36W with over 4 hours duration and 12VDC 72W with over 8 hours duration.

CIRCUITRY

- 120/347V AC 60Hz input, field selectable
- 1.9W power consumption on AC input for LED exit portion of combination sign
- LED Emergency DC wattages as follows: 6VDC = 0.9W; 12VDC = 1.8W
- 6VDC 36W or 12VDC 72W emergency power output versions (as specified)
- Momentary push button test switch
- Pilot LED for AC ON and CHARGE
- · Fully automatic, current limited charger
- Solid state design and construction
- Brownout and short circuit protection
- Temperature compensated
- Maintenance free, sealed lead acid battery




MECHANICAL

- 20 Gauge steel construction
- Slide out faceplates and backplates for rapid and simple installation
- Universal spider knockout pattern stamped into backplate for junction box mounting
- Universal models include ceiling or end mount, field installable canopy kit c/w spider plate
- Front head mounting is standard
- Multiple conduit entry knockouts
- · White powder coat finish standard
- · PAR18 small style, high impact thermoplastic heads
- LED heads with limited lifetime warranty*

DIMENSIONS



Type RMSM - PAR18
Thermoplastic



ORDERING GUIDE



MODEL RATING

		Wattage capacities			
Model	Voltage	30 min.	60 min.	90 min.	120 min.
CXST-2L	6V	36	18	12	9
CXST12-2L	12V	72	36	24	18

^{*} For complete warranty details, please see our terms and conditions in our website

