

**M18™ FORCE LOGIC™
6T Crimper Kit w/ D3
Grooves and Fixed BG Die Kit**

2678-22BG

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Enabled
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Crimping Jaw with Fixed BG Die, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag



**M18™ FORCE LOGIC™
6T Crimper Kit w/ D3
Grooves and Fixed O Die Kit**

2678-22O

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Enabled
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Crimping Jaw with Fixed O Die, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag



**M18™ FORCE LOGIC™
6T Crimper Kit w/ D3
Grooves and Snub Nose**

2678-22

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Enabled
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Snub Nose Crimping Jaw, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag



**M18™ FORCE LOGIC™
6T Utility Crimper Kit
w/ Kearney Grooves**

2678-22K

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Enabled
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Kearney Crimping Jaw, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag




**M18 FORCE LOGIC™
CRIMPERS AND CUTTERS**

See page 55 for details

**M18™ FORCE LOGIC™
600 MCM Crimper**

2679-22

Specifications:

UL Classification	Yes (All 7 Manufacturers)
Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Enabled
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Commercial U Crimping Jaw, Multi-Voltage Charger, Carrying Case



**M18™ FORCE LOGIC™
Cable Cutter Kit
w/ 750 MCM Cu Jaws**

2672-21

Specifications:

Capacity	750 MCM Cu / 1,000 Al
Average Cut Speed	3 Seconds
Head Rotation	350°
Auto Reset	Yes
Length	14"

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, 750 MCM Cable Cutter Jaw, Allen Wrench, Multi-Voltage Charger, Carrying Case



**M18™ FORCE LOGIC™
Cable Cutter Kit
w/ 477 ACSR Jaws**

2672-21S

Specifications:

Capacity	477 HEN ACSR
Average Cut Speed	3 Seconds
Head Rotation	350°
Auto Reset	Yes
Length	14"

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, 477 ACSR Cutting Jaw, Carabiner, Allen Wrench, AC/DC Wall and Vehicle Charger, Bucket Bag



**M18™ FORCE LOGIC™
6 Ton Knockout Tool Kit**

2677-21 (2677-20 No Punches or Dies)

Specifications:

Mild Steel Capacity	4" in 14 Gauge
Stainless Steel Capacity	2" in 14 Gauge
Output Force	6 Ton
Quick-Connect Draw Stud	Yes
Weight	4.3 lbs
Height	4.5"

Includes: 2677-21 (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, EXACT™ 1/2" to 2" Conduit Punches and Dies, (2) Draw Studs, Quick Connect Alignment System, Multi-Voltage Charger, Carrying Case; 2677-20 Includes no Punches or Dies



**M18™ FORCE LOGIC™
10 Ton Knockout Tool Kit**

2676-23, 2676-22 (2676-20 No Punches or Dies)

Specifications:

Mild Steel Capacity	4" in 10 Gauge
Stainless Steel Capacity	4" in 12 Gauge
Output Force	10 Ton
Quick-Connect Draw Stud	Yes
Tool Weight	7.2 lbs
Height	5-1/2"

Includes: 2676-23 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, EXACT™ 1/2" – 4" Conduit Punches and Dies, (3) Draw Studs, Quick Connect Alignment System, Multi-Voltage Charger, Carrying Case; 2676-22 Includes 1/2" – 2" EXACT™ Knockout Punches and Dies; 2676-20 Includes no Punches or Dies




**M18 FORCE LOGIC™
KNOCKOUTS**

See page 57 for details

**M18™ FORCE LOGIC™
Press Tool Kit**

2673-22 (2673-20 No Jaw Kit)

Specifications:

Capacity	1/2" – 4" CU, 1/2" – 1" SS
Weight	8.0 lbs
Length	16-3/4"
Calibration Interval	40,000 Cycles (LED Indicator)
Approximate Cycle Time	5 Seconds
Press Force	7,200 lbs

Includes: 2673-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (6) Jaws 1/2" – 2", Multi-Voltage Charger, Carrying Case; 2673-20 Includes No Jaws




**M12 M18 FORCE LOGIC™
PRESS TOOLS**

See page 53 for details

**M18™ FORCE LOGIC™
Long Throw
Press Tool Kit**

2673-22L (2673-20L No Jaw Kit)

Specifications:

Capacity	1/2" – 4" CU, 1/2" – 2" SS
Weight	10.1 lbs
Length	20-1/8"
Calibration Interval	40,000 Cycles (LED Indicator)
Approximate Cycle Time	5 Seconds, 10 Seconds at Full Stroke
Press Force	7,200 lbs

Includes: 2673-22L (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (3) Jaws 1/2" – 1", Multi-Voltage Charger, Carrying Case; 2673-20L Includes No Jaws

