

**M18™ Multi-Tool Kit**

2626-22 (2626-20 Tool-Only)

**Specifications:**

Speed Settings	12
OPM	11,000 – 18,000
Universal Adapter	Yes
Tool Free Accessory Change	Yes
Length	14"
Weight	4.2 lbs

**Includes:** (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Wood Cutting Blade, Sanding Pad, (5) Assorted Sanding Sheets, Multi-Voltage Charger, Contractor Bag



**M18™ Band Saw Kit**

2629-22 (2629-20 Tool-Only)

**Specifications:**

SFPM	480
Cut Capacity	3-1/4" x 3-1/4"
Shoe	Tool Free
LED Light	Yes
Weight	10.2 lbs

**Includes:** (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Blade, Multi-Voltage Charger, Carrying Case



**M18 FUEL**

**10" Dual Bevel Sliding Compound Miter Saw Kit**

2734-21HD (2734-20 Tool-Only)

**Specifications:**

Blade Size	10"
No Load RPM	4,000
Max Bevel Angle	48° / 48°
Max Miter Angle	50° / 60°
Max Vertical Capacity	5-3/4"
Max Horizontal Capacity	2x12
Weight	47.0 lbs

**Includes:** (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Blade Wrench, Carbide Tipped Blade, Clamp, Dust Bag, Rapid Charger



**M18™ Cut Out Tool Kit**

2627-22, 2627-22CT (2627-20 Tool-Only)

**Specifications:**

RPM	28,000
Tool Free Adjustment	Yes
LED Light	Yes
Belt Clip	Yes
Length	8-9/10"
Weight	1.9 lbs

**Includes:** 2627-22 (2) M18™ REDLITHIUM™ Extended Capacity XC Battery Packs, Belt Clip, (2) 1/8" Drywall Bits, 1/8" Collet, 1/4" Collet, Wrench, Multi-Voltage Charger, Contractor Bag; 2627-22CT Includes (2) M18™ REDLITHIUM™ Compact Battery Packs



**M18 FUEL**

**16 Gauge Angled Finish Nailer Kit**

2742-21CT (2742-20 Tool-Only)

**Specifications:**

Nail Diameter	16 gauge
Nail Size	1-1/4" – 2-1/2"
Nail Collation Angle	20°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Bottom Load
Length	11-9/10"
Weight	7.2 lbs

**Includes:** (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag



**M18 FUEL**

**Metal Cutting Circular Saw Kit**

2782-22 (2782-20 Tool-Only)

**Specifications:**

RPM	3,900
Blade Size	5-3/8" – 5-7/8"
Arbor Size	20 mm
Hang Hook	Yes
Length	4-7/10"
Weight	6.5 lbs

**Includes:** (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, 30T Blade, Multi-Voltage Charger, Contractor Bag



**M18 FUEL**

**18 Gauge Brad Nailer Kit**

2740-21CT (2740-20 Tool-Only)

**Specifications:**

Nail Diameter	18 gauge
Nail Size	5/8" – 2-1/8"
Nail Collation Angle	0°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Side Load
Length	11-2/5"
Weight	6.1 lbs

**Includes:** (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag



**M18 FUEL**

**15 Gauge Finish Nailer Kit**

2743-21CT (2743-20 Tool-Only)

**Specifications:**

Nail Diameter	15 gauge
Nail Size	1-1/4" – 2-1/2"
Nail Collation Angle	34°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Bottom Load
Length	11-9/10"
Weight	7.2 lbs

**Includes:** (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag



**M18 FUEL**

**Deep Cut Band Saw Kit**

2729-22HD, 2729-22, 2729-21 (2729-20 Tool-Only)

**Specifications:**

SFPM	0 – 380
Cut Capacity	5" x 5"
Shoe	Tool Free
LED Light	Yes
Hang Hook	Yes
Weight	15.9 lbs

**Includes:** 2729-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Blade, Rapid Charger, Carrying Case; 2729-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2729-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger



**M18 FUEL**

**16 Gauge Straight Finish Nailer Kit**

2741-21CT (2741-20 Tool-Only)

**Specifications:**

Nail Diameter	16 gauge
Nail Size	3/4" – 2-1/2"
Nail Collation Angle	0°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Bottom Load
Length	11-9/10"
Weight	7.2 lbs

**Includes:** (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag

