

M18™ Jobsite Radio

2890-20

Specifications:

Modes	AM, FM, AUX
Tuner	Digital Processor w/ 10 Station Presets
USB Charging Port	2.1 Amps
Device Storage	Weather Sealed Auxiliary Compartment
Powered By	All M18™ Batteries, 120V AC



Battery and Charger Sold Separately

Includes: 6" Auxiliary Cord, (2) AAA Batteries (For Memory Backup)

M18™ / M12™ Wireless Jobsite Speaker

2891-20

Specifications:

Modes	Bluetooth, AUX (Cable Not Included)
Bluetooth Range	100 ft
USB Charging Port	2.1 Amp
Powered By	All M18™ and M12™ Batteries



Battery and Charger Sold Separately

Includes: AC Adapter

M18™ Power Source

49-24-2371

Specifications:

Powered By	All M18™ Batteries
Run-Time	Up to 18 Hours
2.1 Amp USB Port	Universal Charging for Smartphones, Tablets and Other Portable Electronic Devices



Battery Sold Separately

Powers all MILWAUKEE® M12™ Heated Gear



M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 System Starter Kit

48-59-1890


Includes: (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Rapid Charger



M18™ REDLITHIUM™ XC5.0 System Starter Kit

48-59-1850


Includes: (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, Multi-Voltage Charger



M18™ REDLITHIUM™ XC System Starter Kit

48-59-1813

Includes: (1) M18™ REDLITHIUM™ XC Battery Pack, Multi-Voltage Charger



M18™ and M12™ Multi-Voltage Charger

48-59-1812

Specifications:

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

M18™ and M12™ Rapid Charge Station

48-59-1807

Specifications:

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Charges 3 Batteries Simultaneously
Charge Speed	Charges Individual Batteries up to 40% Faster
Capacity	Holds (3) M18™ and (3) M12™ Batteries
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes
Pass-Through Plug	Yes



Batteries Sold Separately



M18™ and M12™ Rapid Charger

48-59-1808

Specifications:

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Charge Speed	Charges Individual Batteries up to 40% Faster
On-Board Indicator Light	Yes
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

M18™ Six-Pack Sequential Charger

48-59-1806

Specifications:

Compatibility	All M18™ Batteries
Charge Sequence	Sequential (Counter-Clockwise Rotation)
Skip Button	Manually Designate which Battery Charges First
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes
Pass-Through Plug	Yes



Batteries Sold Separately



M18™ AC/DC Wall and Vehicle Charger

2710-20

Specifications:

Compatibility	All M18™ Batteries
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



FULL SYSTEM COMPATIBILITY

COMPACT

- Less weight and smaller size for light drilling and fastening



EXTENDED CAPACITY

- More power and run-time, great performance for all demands



HIGH DEMAND™

- Best performance for high demand applications



LIGHT APPLICATIONS

OPTIMIZING PERFORMANCE AT EVERY LEVEL

All M18™ REDLITHIUM™ batteries are compatible with all M18™ tools

HEAVY APPLICATIONS

COMPACT

- Lighter weight for less fatigue
- Compact size for increased versatility

M18™ REDLITHIUM™ 2.0 Compact Battery Pack

48-11-1820



M18™ REDLITHIUM™ Compact Battery Pack

48-11-1815

2-Pack Available

48-11-1811



EXTENDED CAPACITY

- Double the run-time of compact packs
- Increased performance and power

M18™ REDLITHIUM™ XC6.0 Extended Capacity Battery Pack

48-11-1860



M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack

48-11-1850

2-Pack Available

48-11-1852



M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack

48-11-1840

10-Pack Available

48-11-1841



M18™ REDLITHIUM™ XC Extended Capacity Battery Pack

48-11-1828

2-Pack Available

48-11-1822



HIGH DEMAND

- Double the run-time of XC packs
- Highest power output
- Runs coolest in heavy application

M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack

48-11-1890



UP TO
5X
MORE
RUN-TIME

UP TO
35%
MORE
POWER

RUNS
UP TO
60%
COOLER



M18™ COMBO KITS

M18™ COMBO KITS	2 PIECE KITS															4 PIECE KITS				LARGE KITS			
	2796-22	2897-22	2799-22CX	2697-22	2697-22CT	2795-22	2798-22CT	2691-22	2894-22	2694-22	2695-22	2899-22	2896-22	2896-22CT	2896-24	2694-24	2695-24	2696-24	2896-26	2696-26	2696-29	2695-15	
Kit Tool Total	2	2	2	2	2	2	2	2	2	2	2	2	2	2	4	4	4	4	6	6	9	15	
M18 FUEL™ 1/2" Hammer Drill/Driver w/ ONE-KEY™	■																						
M18 FUEL™ 1/2" Hammer Drill/Driver		■							■			■			■				■				
M18™ 1/2" Compact Brushless Hammer Drill/Driver			■																				
M18™ 1/2" Compact Hammer Drill/Driver				■	■					■	■					■	■	■		■	■	■	
M18 FUEL™ 1/2" Drill/Driver w/ ONE-KEY™						■																	
M18 FUEL™ 1/2" Drill/Driver																							
M18™ 1/2" Compact Brushless Drill/Driver							■																
M18™ 1/2" Compact Drill/Driver								■															
M18™ 3/8" Right Angle Drill/Driver																					■	■	
M18 FUEL™ Drywall Screw Gun													■	■									
M18 FUEL™ 1/4" Hex Impact Driver w/ ONE-KEY™	■					■																	
M18 FUEL™ SURGE™ 1/4" Hex Hydraulic Driver												■	■	■									
M18 FUEL™ 1/4" Hex Impact Driver		■													■				■				
M18™ 1/4" Hex Brushless Impact Driver			■				■																
M18™ 1/4" Hex Impact Driver*				■	■			■									■	■		■	■	■	
M18™ 5/8" SDS Plus Rotary Hammer																						■	
M18™ 1/2" High Torque Impact Wrench																					■	■	
M18™ 1/2" Compact Impact Wrench																						■	
M18 FUEL™ SAWZALL® Recip Saw									■						■				■				
M18™ SAWZALL® Recip Saw										■						■				■	■	■	
M18™ HACKZALL® One-Handed Recip Saw											■						■						
M18 FUEL™ 6-1/2" Circular Saw																			■				
M18™ 6-1/2" Circular Saw																■				■	■	■	
M18™ Jig Saw																					■	■	
M18™ Multi-Tool																						■	
M18™ Band Saw																						■	
M18™ 5-3/8" Metal Cutting Saw																						■	
M18 FUEL™ 4-1/2" / 5" Grinder Paddle Switch, No-Lock Kit																			■				
M18™ 4-1/2" Cut-Off / Grinder																				■	■	■	
M18™ Compact Blower																						■	
M18™ LED Work Light															■	■	■	■	■	■	■	■	
Also Includes	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	
M18™ and M12™ Multi-Voltage Charger	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■		
M18™ Six-Pack Sequential Charger																						■	
M18™ REDLITHIUM™ Compact Battery Pack					2			2															
M18™ REDLITHIUM™ 2.0 Compact Battery Pack			1				2							2									
M18™ REDLITHIUM™ XC Extended Capacity Battery Pack				2							2					2	2	2		2	2		
M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack			1																			4	
M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack	2	2				2			2	2		2	2		2				2				
Carrying Case	■	■				■						■											
Contractor Bag			■	■	■		■	■	■	■	■		■	■	■	■	■	■	2	■	2	3	

*M18™ 1/4" Hex Impact Driver is the single, variable speed model

