



USB CHARGERS WITH DUPLEX 15A TAMPER-RESISTANT OUTLETS, WHITE

TM826USBWCC6 | [radiant](#)

FEATURES & BENEFITS

The radiant® collection is a step up from the standard with simple, classic options in wiring devices, home automation controls and screwless wall plates that complement today's homes.

radiant® USB charging solutions let you charge more of your devices without the need for bulky AC adapters.

radiant® Screwless Wall Plate not included.

For detailed information on USB Charging Devices, visit our [USB Charging page](#).

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).



- Charge two mobile phones or tablets simultaneously while enjoying the added power convenience of a tamper-resistant outlet.
- Compatible with USB 2.0 & 3.0 compatible devices.
- Total charging capacity of 3.1A, shared between both ports.
- Power outlets meet NEC® Tamper-Resistant requirements.
- Protects children: patented shutter system helps prevent improper insertion of foreign objects—now with black "invisi-shutters" for an invisible effect preferred by end users.
- Back and side wire terminals accommodate #10-#14 AWG stranded and solid copper wire for installation flexibility; tightening torque: 12-14 lbf-in.
- For covering patents, see www.legrand.us/patents.
- The external brass backwire pressure-plate and posted side-wire terminal screws make installation fast and easy.
- RoHS compliant

SPECIFICATIONS

GENERAL INFO

Color: White

Special Features: 3.1 Amps of total charging capacity

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.2 No. 42; C22.2 No. 223

CSA Standard: Yes

cULus: Yes

UL Listing No: UL498; UL1310

UL Standard: Yes

CONSTRUCTION INFORMATION

Component 4: 78500703216

DIMENSIONS

Depth (US): 1.39"

Height (US): 2.67"

Width (US): 1.69"

TECHNICAL INFORMATION

Amps: 15A

NEMA Configuration Number: 5-15R

Volts: 125V

COUNTRY OF ORIGIN

Country Of Origin: CHINA