

## **Overhead Anchoring**

- 3/4" Embedment
- Flush Mounted
- Internally Threaded
- For Cracked and Uncracked Concrete



## Mini-Undercut+<sup>™</sup>



### ENGINEERED BY **POWERS**

**Hollow Core Concrete** 







**CODE APPROVE** 3/4" long approved seismic anchor

**STOP BIT** widened shoulder eliminates potential for over drilling; solid carbide head for quick drilling

for fast installation

internally tapped sleeve provides full thread engagement

patent pending design bites into concrete for undercut



# Mini-Undercut+<sup>™</sup> Internally Threaded Undercut Anchor



### Mini-Undercut+

CATALOG	ANCHOR	rod	DRILL	QTY	MASTER
NUMBER	SIZE	Dia	DIA		QTY
PFM2111820	3/8" x 3/4"	3/8"	5/8"	100	600
CATALOG	USE		USE		
NUMBER	ACCU-BIT		SDS+ SETTING TOOL		
PFM2111820	PPA2431720		PFM2101720		

### Accu-Bit

CATALOG	STOP BIT	rod	DRILL	DRILL	QTY
NUMBER	SIZE	Dia	DIA	DEPTH	
PPA2431720	5/8" x 3/4"	3/8"	5/8"	3/4"	1

### **SDS+ Setting Tool**

CATALOG	SETTING	ROD	QTY
NUMBER	TOOL SIZE	DIA	
PFM2101720	3/8" SDS+ Setting Tool	3/8"	1

### **Installation Systems**

CATALOG NUMBER	DESCRIPTION	
DCH273P2	20V MAX* XR Brushless 1" L-shape SDS Plus Rotary Hammer Kit	121

Maximum initial battery voltage (measured without a workload) is 20 volts. Nominal voltage is 18.



 $\label{eq:copyright} \verb"©" 2017 DEWALT. The yellow/black color scheme is a trademark for DEWALT power tools, accessories, anchors & concrete adhesives.$ 

Dealer Stamp