

## TYPE MT-25

### Features

- Dieless single indent compressor
- Steel adjusting knob
- UL Listed terminals and splices
- Broad wire range
- Mounting hole for bench mounting applications

### Benefits

- Reduces installed cost by having no separate dies to purchase, change or lose
- Provides fast and easy setting. Simply align the line on the die nest with the wire size gauge for proper crimping results.
- Ensures reliability. ILSCO's standard line of connectors are UL Listed when crimped with the MT-25 tool
- Convenience

### Specifications

Length: 22.65"  
Weight: 6 lbs.  
Depth: 4.86"  
Width: 1.12"  
Conductor Range: 4/0-8 AL  
250kcmil-8 CU



### For Use with

Aluminum Connectors	Copper Connectors
ACL, ACN 4/0-8	CLN4, CLN9, CLND,
2ACL, 2ACN 4/0-8	CLNF, CLNN, CLNS,
AS 4/0-8	CLNU, CLW4, CLW9,
Series:ALNS, ALND, ASN,	CLWD, CLWF, CLWN,
ALNN thru 4/0	CLWS, CSN4, CSN9,
	CSND, CSNF, CSNN,
	CSNS, CSW4, CSW9,
	CSWD, CSWF, CSWN,
	CSWS thru 250kcmil
	CCL, CRAM

All wire sizes, unless noted otherwise, are American Wire Gauge (AWG)