



C11LH3

by Burndy
Catalog ID: C11LH3

Prop 65 Notice

Cast Bronze Clamp,Cable to Water Pipe, 3/0 AWG - 10 AWG, 1/2" - 1" Water Pipe, 1" hub.

Features: For Grounding Rigid Conduit Systems, Continuity From Rigid Conduit Systems To Ground Provided By Cast Bronze Threaded Conduit Hub, Zinc Plated Screws, C-LH Parts Ending In "-3" Have Two Screws, Hub Size: 1 IN, Water Pipe Size: 3/8 - 1 IN, Installation Torque: 50 IN-LB For Pipe And Wire Clamp, Cross Flats: 1.19 IN, Length: 2.86 IN, Width: 1.13 IN, Height: 2.69 IN, Armored Cable: No, Ground Strap: No

Product Details

General

Application	For Grounding Rigid Conduit Systems
Material	Bronze Alloy
Material - Hardware	Zinc Plated Steel
Plated	N
Plating Type	Unplated
Sub Brand	CONDUIT
Type	Ground Clamp
UPC	781810142165
UPC 12 Digit	7818101421655

Dimensions

Dimension - Height inch	2.69 in
Dimension - L Length Overall mm	73 mm
Dimension - Length Overall inch	2.86 in
Dimension - Pad Width inch	1.19 in
Dimension - Width inch	1.13 in
Dimension - Width mm	29 mm

Conductor Related

Conductor - Armored Cable Size	N
Conductor - Copper Str Size	10 AWG;9 AWG;8 AWG;7 AWG;6 AWG;5 AWG;4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG
Conductor - Copper Str Size Range	10 AWG-3/0 AWG
Conductor - Pipe EMT Size	1/2 in;3/4 in;1 in
Conductor - Pipe EMT Size Range	1/2 in-1 in

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No

Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	NC
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)