



RDM428

by Burndy
Catalog ID: RDM428

Prop 65 Notice

URD Mole, #4 Str. - 250 kcmil Al or Cu 300 kcmil - 350 kcmil , 600 Volt Rating, 5.81 in L.

Features: Type RDM-28 MOLE Is An Economical, Insulated, Submersible Service Junction Suitable For Direct Burial Or For Use In Enclosures, Disconnectable Joints Allow Additions Of New Services Without Disturbing Previous Installations, Taping Is Eliminated, Heat-Shrink Or Force-Fit Rubber Sleeves Insulate Each Joint, Rubber Is Used To Insulate The MOLE Body, Removable Sealing Covers Are Supplied On All Outlets But Two, REA Listed Tap Kits, Including HYLUG, Hardware And Sleeve Are Ordered Separately, Number Of Outlets: 4

Product Details

General

| | |
|-------------------|--|
| Application | For Aluminum And Copper And Direct Burial Or For Use In Enclosures |
| Connector Type | Tap |
| Insulation | Y |
| Insulation Type | Rubber |
| Material | Aluminum Alloy |
| Number Of Outlets | 4 |
| Sub Brand | URD MOLE |
| Trade Name | MOLE™ |
| Type | RDM-28 |
| UPC | 781810180006 |
| UPC 12 Digit | 7818101800066 |

Dimensions

| | |
|---------------------------------|---------|
| Dimension - Length Overall inch | 5.81 in |
|---------------------------------|---------|

Conductor Related

| | |
|-----------------------------------|---|
| Conductor - AL Str Size | 4 AWG;3 AWG;2 AWG;1 AWG;1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil |
| Conductor - AL Str Size Range | 4 AWG-350 kcmil |
| Conductor - Copper Str Size | 4 AWG;3 AWG;2 AWG;1 AWG;1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil |
| Conductor - Copper Str Size Range | 4 AWG-250 kcmil |

Certifications and Compliance

| | |
|------------------------------------|----|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | No |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)