



Q3A344N

by Burndy
Catalog ID: Q3A344N

Prop 65 Notice

Copper Terminal, 4 Hole, 400-500 kcmil, 1/2" Stud, 1-3/4" Stud Hole Spacing, 3 Screws.

Features: Compact, high copper alloy terminal for joining three cables to equipment pads or bar, Each element accommodates a wide range of cable

Product Details

General

| | |
|---------------------------------------|-------------------------|
| Application | For Copper Cable |
| Connector Type | Terminal |
| Installation Torque Recommended in-lb | 375 LBS/in |
| Material | Copper |
| Physical Attribute - Number of Holes | 4 |
| Physical Attribute - Number of Screws | 3 |
| Physical Attribute - Screw Type | Hexagonal Bolt |
| Plated | N |
| Plating Type | Unplated |
| Sub Brand | QIKLUG |
| Temperature Rating | 194 |
| Trade Name | QIKLUG™ |
| Type | Bolted Lugs & Terminals |
| UPC | 781810323649 |
| UPC 12 Digit | 7818103236499 |

Dimensions

| | |
|---|-----------|
| Dimension - D inch | 3.13 in |
| Dimension - F Width Center to Center inch | 1.75 in |
| Dimension - Height fraction | 1-15/16 |
| Dimension - Height inch | 2.00 in |
| Dimension - Hole Size fraction | 9/16 |
| Dimension - Hole Size inch | 0.56 in |
| Dimension - Hole Size mm | 14 mm |
| Dimension - L Length Overall mm | 119 mm |
| Dimension - Length Overall inch | 4.69 in |
| Dimension - N inch | 0.63 in |
| Dimension - Pad Width inch | 3.00 in |
| Dimension - Stud Size inch | 1/2 |
| Dimension - Width fraction | 4-9/16 in |

| | |
|------------------------|---------|
| Dimension - Width inch | 4.56 in |
| Dimension - Width mm | 116 mm |

Electrical Ratings

| | |
|--------------------------|-----|
| Rating - Minimum Voltage | 600 |
|--------------------------|-----|

Conductor Related

| | |
|-----------------------------------|--|
| Conductor - Copper Str Size | 400 Kcmil;500 Kcmil |
| Conductor - Copper Str Size Range | 400 Kcmil-500 Kcmil |
| Conductor Type | <ul style="list-style-type: none"> • CU C Str-Size • CU C Solid-Size |

Certifications and Compliance

| | |
|------------------------------------|-------------|
| Certification - CSA Approved | No |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Industry Standard(s) | UL468A-468B |
| Standards - Industry Standards Met | UL468A-468B |
| Standards - RoHS Compliance Status | EX |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)