



PAT60018V

by Burndy
Catalog ID: PAT60018V

Prop 65 Notice

Battery Actuated Tool, Hydraulic self-Contained, 6 Ton, 18V Ni-MH.

- Specialized latch head design
- Ergonomic design allows one hand operation for Ram advance and Ram retraction
- 180 degree head rotation
- Permanent D3 crimp groove accepts all W Dies
- Enhanced clearance for tap connections

Battery powered crimp technology, Advance design high speed pump completes crimp in approximately 3 seconds 5 Year Limited Warranty on Tool, 1 Year on Batteries and Charger

Product Details

General

Application	For Use On: 8 AWG - 600 KCMIL Copper Stranded (YA, YA-L,YS, YS-L), 8 AWG - 350 KCMIL Flex, 8 - 350 KCMIL Aluminum (YA-A And YS-A)
Battery Type	Nickel Metal Hydride (NiMH)
Crimp Force Capacity	6 ton
Die Type	W, V, W-VT style dies
Recharge Time	0.75 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810361276
UPC 12 Digit	7818103612766

Dimensions

Height	13.75 in
Length	14.5 in
Weight	10.9 lb
Width	3.5 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges	#8 - 600 kcmil Copper Str. (YA, YA-L, YS, YS-L), #8 - 350 kcmil Flex, #8 - 350 kcmil Aluminum (YA-A & YS-A)
-----------------	--

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No

Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)