



K22A39U2

by Burndy Catalog ID: K22A39U2

Prop 65 Notice

Aluminum Universal Terminal, 2 Hole, Four: 1/0 AWG (Str)-750 kcmil, 3/8" Stud, 1.38" Stud Hole Spacing, 4 Screws, Al/Cu Rated, Tin Plated.

Universal terminal, These dual-rated panelboard lugs are constructed from high strength extruded aluminum alloy and electro tin-plated to provide low contact resistance

Product Details

General

| Application | For Aluminum and Copper Conductors |
|---------------------------------------|------------------------------------|
| Connector Type | Terminal |
| Installation Torque Recommended in-lb | 375 LBS/in |
| Material | Aluminum |
| Material - Hardware | Aluminum |
| Physical Attribute - Number of Holes | 2 |
| Physical Attribute - Number of Screws | 4 |
| Physical Attribute - Screw Type | Allen |
| Plated | Y |
| Plating Type | Tin plated |
| Sub Brand | UNIVERSAL TERM |
| Temperature Rating | 194 |
| Туре | Bolted Lugs & Terminals |
| UPC | 781810370339 |
| UPC 12 Digit | 7818103703399 |

Dimensions

| Dimension - Bolt Hole Size inch | 0.38 in |
|---------------------------------|-----------|
| Dimension - D inch | 2.31 in |
| Dimension - Height fraction | 3 in |
| Dimension - Height inch | 3.02 in |
| Dimension - Hole Size inch | 0.41 in |
| Dimension - Hole Size mm | 10 mm |
| Dimension - L Length Overall mm | 125 mm |
| Dimension - Length Overall inch | 4.91 in |
| Dimension - N inch | 0.38 in |
| Dimension - Pad Width inch | 2.86 in |
| Dimension - Stud Size inch | 3/8 in |
| Dimension - Width fraction | 3-3/50 in |
| Dimension - Width inch | 2.86 in |

| Conductor Related | | |
|-----------------------------------|---|--|
| Conductor - AL Str Size | 1/0 AWG;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;266 kcmil;300 kcmil;336 kcmil;350 kcmil;397 kcmil;400 kcmil;450 kcmil;477 kcmil;500 kcmil;550 kcmil;556 kcmil;600 kcmil;636 kcmil;650 kcmil;700 kcmil;715 kcmil;750 kcmil | |
| Conductor - AL Str Size Range | 1/0-750 Acmil | |
| Conductor - Copper Str Size | 1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil;500 kcmil;600 kcmil;700 kcmil;750 kcmil | |
| Conductor - Copper Str Size Range | 1/0-750 Acmil | |
| Conductor Type | AL C Str-SizeCU C Str-Size | |

78 mm

600

Certifications and Compliance

Number Of Conductors

Dimension - Width mm

Rating - Minimum Voltage

Electrical Ratings

| Certification - CSA Approved | Yes |
|---|--------------|
| Certification - UL Listed Direct Burial | No |
| Industry Standard(s) | UL 486A-486B |
| Standards - Industry Standards Met | UL 486A-486B |
| Standards - RoHS Compliance Status | NC |
| UL Listed | Yes |

4

Logistics

| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday Emergency Service 24-hours/365 Days

Phone: 1-800-346-4175

1-603-647-5299 (International)