



YSV2CL

by Burndy
Catalog ID: YSV2CL

Prop 65 Notice

Copper Compression Splice, AN-2, 1.41" Splice Length, Short Barrel, Tin Plated.

Features: HYLINK Type YSV-L Seamless Splice Connector Is Used To Splice Type AN Aircraft Cables Plus Commercial Stranded And Solid AWG Conductors, Suitable For Aircraft, Light Duty Industrial And General Purpose Applications, Tools, Die Nest Catalog Number, Die Indentor Catalog Number: HYPRESS: H35, Y35BH, Y39, Y39BH Tool, UV2L Die Nest, Y34PLA Die Indentor, Y35P3 Indentor Adaptor, Conductor Type: Commercial/Aircraft Stranded Copper, Installation Tool: Ratchet: YIMRTC, HYTOOL: Type AH, Aircraft, Cable - MY28 Tool, All Others: MY29-3, MY29-11 Tool, 1 Crimp, Wire Strip Length: 5/8 IN, Insulation Support: No

Product Details

General

| | |
|------------------------|--|
| Application | For Aircraft, Light Duty Industrial And General Purpose Applications |
| Connector Type | Splice |
| Die Index | 41 |
| Feature - Barrel Style | Chamfered |
| Material | Copper |
| Plated | Y |
| Plating Type | Tin |
| Sub Brand | HYLINK |
| Trade Name | HYLINK™ |
| Type | Splice |
| UPC | 781810543894 |

Dimensions

| | |
|-----------------------------------|---------|
| Dimension - B Length fraction | 5/8 in |
| Dimension - B Length inch | 0.62 in |
| Dimension - L Length Overall mm | 36 mm |
| Dimension - Length Overall inch | 1.41 in |
| Dimension - Outside Diameter inch | 0.46 in |
| Dimension - Strip Length inch | 5/8 in |

Electrical Ratings

| | |
|-------------------|-------|
| Voltage - Maximum | 600 V |
|-------------------|-------|

Conductor Related

| | |
|--------------------------------------|-------|
| Conductor - Copper Solid Size | 2 AWG |
| Conductor - Copper Str Aircraft Size | AN 2 |
| Conductor - Copper Str Size | 2 AWG |

| | |
|----------------|--|
| Conductor Type | <ul style="list-style-type: none">• CU C Str-Size• CU C Solid-Size• CU C Str Aircraft-Size |
|----------------|--|

Certifications and Compliance

| | |
|------------------------------------|-----|
| Certification - CSA Approved | Yes |
| Certification - ETL | No |
| Certification - UL Recognized | No |
| Certification - cULus | No |
| Standards - RoHS Compliance Status | CM |
| UL Listed | Yes |

Logistics

| | |
|-----------------------|---|
| Minimum Pack Quantity | 1 |
|-----------------------|---|

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)