



GRL5

by Burndy
Catalog ID: GRL5

Prop 65 Notice

Mechanical Grounding Connector, 10 AWG - 2 AWG, 5/8" Ground Rod.

Features: UL467 Listed, Acceptable For Direct Burial, Economical, Ground Rod Size: 5/8 IN

Product Details

General

Application	For Direct Burial
Material	Copper Alloy
Plated	N
Plating Type	Unplated
Sub Brand	MECHANICAL CONNECTOR
Type	GRL, Light Duty
UPC	781810051825
UPC 12 Digit	7818100518255

Conductor Related

Conductor - Copper Str Size Range	10 AWG-2 AWG
Conductor - Rod Size	5/8 in
Conductor Size	#2 AWG - #10 AWG

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Listed Direct Burial	Yes
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	200 EA
Minimum Pack Quantity	1

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)