



PAT750XT18V

by Burndy
Catalog ID: PAT750XT18V

Prop 65 Notice

Battery Actuated Crimping Tool, Hydraulic Self Contained, 12 Ton Output Force, 14 AWG-750 kcmil Copper, 8 AWG - 750 kcmil Aluminium, 4 AWG - 556.5 kcmil ACSR, 18V Ni-MH, 1/2" - 1" Ground Rod.

- True, one-handed operation for advance, retract, and hold
- 12 ton output force
- State of the art crimping head design, 360° head rotation
- Ergonomically balanced tool design
- Durable High Impact Formed carrying case
- 5-year limited warranty on tool. 3-year warranty on battery and charger

Battery Actuated Crimping Tool, Hydraulic Self Contained, 12 Ton Output Force, 14 AWG-750 kcmil Copper, 8 AWG - 750 kcmil Aluminium, 4 AWG - 556.5 kcmil ACSR, 18V Ni-MH, 1/2 IN - 1 IN Ground Rod 5 Year Limited Warranty on Tool, 3 year on batteries/ charger, Lifetime warranty on INFINITY DRIVE®

Product Details

General

Application	For Use On: 8 AWG Solid - 500 KCMIL Copper, 8 AWG Solid - 587.2 KCMIL Aluminum, 4 AWG - 556.5 KCMIL ACSR (Tension Sleeves), 14 AWG Solid - 500 KCMIL Copper, 8 AWG - 500 KCMIL Aluminum (Taps), Aerial Cable: 6 AWG - 500 KCMIL, 8 AWG - 750 KCMIL Aluminum And Copper, 4 AWG - 556 KCMIL ACSR (Terminals And Splices), 8 AWG - 500 KCMIL Copper (HYGROUND Cable/Ground Rod)
Battery Type	2.6 Ah Ni-MH
Crimp Force Capacity	12 ton
Die Type	U DIE
Recharge Time	0.75 h
Sub Brand	PATRIOT® CRIMPER
Tool Type	Battery Actuated Crimper
Trade Name	PATRIOT®
Type	Crimpers
UPC	781810438701
UPC 12 Digit	7818104387011

Dimensions

Height	13.5 in
Jaw Width	1.65 in
Length	15.75 in
Weight	16.5 lb
Width	3.50 in

Electrical Ratings

Operating Voltage	18 VDC
-------------------	--------

Conductor Related

Crimping Ranges

Tension Sleeves: Copper #8 Sol. To 500 kcmil, Aluminum #8 Sol. To 587.2 kcmil, ACSR #4 to 556.5 kcmil; Taps: Copper #14Sol. To 500 kcmil, Aluminum #8 to 500 kcmil; Aerial Cable Copper #6 to 500 kcmil; Terminals & Splices: Copper #8 to 750 kcmil, Aluminum #8 to 750 kcmil, ACSR #4 to 556 kcmil; HYGROUND: Copper #8 to 500 kcmil, Ground Rods 1/2" to 1" Diameter

Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	EX
UL Listed	No

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters

47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:

8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)