



*Quality Products. Service Excellence.*

## Economy Swing-Out Wall Mount Cabinet *RB-SW Series*

130 lbs (59 kg) Weight Capacity



**RACK BASICS®**



### Features:

- Double-hinged for easy rear access (body swings open to 120°).
- Constructed in light duty 16-gauge steel.
- Includes two (2) pairs of EIA compliant square hole punched rails with 19" mounting.
  - Starter pack of (25) M6 screws and cage nuts included.
  - For 10-32 hardware, see our **CAGKIT Series**.
- Rails are adjustable.
- Includes one (1) locking lightly smoked tempered glass reversible front door (hinged on right side as standard).
- Includes one (1) pair of locking removable side panels.
- Front and side of frame includes venting for air flow.
- Top, bottom and rear cable access.
- Provision for optional fans on top panel.
- Middle body section is not reversible, and hinges on the left side.
- Ships assembled - ready to install.
- Meets PCI DSS (Payment Card Industry Data Security Standard) compliance requirements.
- Finished in black powder paint.
- Tested to 130 lbs (59 kg) of equipment load capacity.
- RoHS Compliant.

Part of the Rack Basics® line of economy rack solutions.

### Accessories

- Horizontal Ring Cable Manager
- Cable Lacing Bar
- Fan Kits
- PDUs and Outlet Strips
- Horizontal Lacing Strip
- Universal Rack Shelf
- Mounting Hardware



Part No.	Overall Dimensions			Rack Units	Mounting Dimensions			Maximum Equipment Depth
	Height	Width	Depth		Height	Width	Depth	
RB-SW9	19.90	23.62	21.65	9U	15.75	19.00	16.13	20.00
RB-SW12	25.15	23.62	21.65	12U	21.00	19.00	16.13	20.00
RB-SW15	30.40	23.62	21.65	15U	26.25	19.00	16.13	20.00
RB-SW18	35.65	23.62	21.65	18U	31.50	19.00	16.13	20.00

Note: Usable depth is the furthest depth equipment can be mounted for the cabinet's swing-out feature to function.

*Data subject to change without notice*

© 2021. Hammond Manufacturing Ltd. All rights reserved.