

# PASS & SEYMOUR®

radiant® Spec Grade Receptacles Tamper-Resistant 20A, 125V




**TR26352RLA** 

# Style meets safety in radiant® Spec Grade Tamper-Resistant Receptacles.

#### TR26352R

Part of the radiant® collection of wiring devices, screwless wall plates, and home automation controls, these receptacles feature a corrosion-resistant plated-steel mounting strap, durable nylon face, and triple-wipe power contacts combined with tamper-resistant shutters to deliver safe and reliable performance. Ergonomic radiant styling offers a sleek design, while giving the same performance and ease of installation as standard Pass & Seymour devices. Tamper-resistant feature helps you comply with 2014 NEC® Article 406.12 and gets the job done right. Screw-pressure-plate back wiring ensures easy installation and excellent electrical connections. These UL-Listed receptacles are ideal for residential, multi-dwelling, commercial office, and hospitality applications.


#### Features & Benefits



# **3rd Party Compliance**



c(UL) us UL Listed, File Number E140596, Standard UL498, CSA Certified, File Number LR16063, Standard CSA-C22.2 No. 42, Conforms to NEMA WD-1 and WD-6






# **Technical Information**

Performance
-------------

Electrical		
Dielectric Withstand Voltage	Withstands 2000V minimum	
Maximum Working Voltage	250V	
Current Interrupting	Certified for current interrupting at full-rated current	
Temperature Rise	Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current	
Environmental		
Flammability	UL94 V2	
Operating Temperature	Maximum continuous +60°C, minimum -40°C without impact	
Mechanical		
Terminal Identification	Terminal Identification in accordance with UL 49 (Brass, White, Green)	
Terminal Accommodation	#14 AWG - #10 AWG copper conductor only	
Product Identification	Ratings are permanent part of the device	



TR26352RLA

#### **Materials**

Face	Nylon
BackBody	Nylon
Line Contacts	.032 260 Brass
Mounting Strap	.042 Zinc-Plated Steel
Ground Contacts	.040 260 Brass
Pressure Plate	.080 Steel
Tamper-Resistant Shutters	Thermoplastic
Terminal Screws	#8 Tri-Drive Steel (Neutral = Nickel-Plated Steel)
Ground Screw	#8 Hex Tri-Drive Steel; Zinc Coating with Green Chromate
Auto-Ground Clip	Steel
Mounting Screws	Tri-Drive Steel

# Warranty

1 Year





radiant® Spec Grade Receptacles Tamper-Resistant 20A, 125V

# **Ordering Information**

# radiant® Spec Grade Receptacles Back & Side Wire

	Rating			NEMA
<b>Catalog Number</b>	Α	V	Color	Configuration No.
TR26352RI	20A	125V	Ivory	5-20R
TR26352RW	20A	125V	White	5-20R
TR26352R	20A	125V	Brown	5-20R
TR26352RGRY	20A	125V	Gray	5-20R
TR26352RBK	20A	125V	Black	5-20R
TR26352RLA	20A	125V	Light Almond	5-20R







radiant® Spec Grade Receptacles Tamper-Resistant 20A, 125V

# Field Uses/Vertical Markets

Residential

Retail

Office

· Hospitality/Lodging

Multiple Dwelling

Education

#### Also available in the radiant® collection...

- GFCI Receptacles
- Tamper-Resistant and Standard Duplex Receptacles
- Paddle Switches
- Fan Controls
- Sensors

- Timers
- Home Automation Controls
- USB Charging Devices
- Night Lights
- Screwless Wall Plates



The paper used to print this document is an environmentally responsible paper with 10% post consumer waste, with FSC and SFI Chain of Custody certifications, Lacey Act complaint. 100% of the electricity used to manufacture Flo sheets is generated with

All brand and product names referenced in this document are registered trademarks or trademarks of their respective holders.



Legrand, North America 60 Woodlawn Street West Hartford, CT 06110 1.877.BY.LEGRAND (295.3472) www.legrand.us

570 Applewood Crescent Vaughan, Ontario L4K 4B4 905.738.9195 www.legrand.ca

