

Project Name

Location

Prepared By



SATCO S39975

15T8/LED/48-830/DR

Notes

[www] 03-15-2021 00:27:52

General

Status	Discontinued
Substitute	S49975
Watts	15
Fluorescent Equivalent	25W-32W
Volts	120V-277V
Ballast Type	Type A
Shape	T8
Base	Medium Bi Pin
ANSI Base	G13
Nominal Length	48
Finish	Gloss White
CCT (Kelvin)	3000
Temperature	Warm White
CRI	82
Lumens	2100
Beam Spread	210
Dimmable	Check Ballast MFG for Dimmer Compatibility
Hours Rated	50000
Lamp Type	Linear
Technology	LED

Electrical

Ballasting Requirements	Ballast required. Direct Replacement-for use on Instant Start and Rapid Start ballasts with no rewiring required. May not be compatible with every ballast. Refer to the ballast compatibility chart
Power Factor	0.9
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

Physical

MOL	48
MOD	1

Additional Information

Warranty	5 Year Limited - T8 LED Bulbs
----------	-------------------------------

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
DLC Approved	Yes
DLC ID	PLKZV3JQASSC
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
NSF Approved	Yes - Approved

