



## KLU400

by Burndy  
Catalog ID: KLU400

Prop 65 Notice

Copper Terminal, Offset Tongue, 1 Hole, 1/0 AWG (Str)-500 kcmil, 3/8" Stud, 1 Screw.

Features: Terminal With Offset Tongue For Joining A Wide Range Of Cable To Equipment Pads Or Bar, Convenient Range-Taking Design, Reduces Catalog Numbers, One Conductor Accommodates Several Conductor Sizes, High Conductivity Copper Alloy, Long Lasting Reliable Contact, Compact Design, Easy To Use, Reduces Labor Time, Slot Robertson Screw, Hex Head/Hex Socket Bolt, No Special Installation Tools Required, Eliminates Over-Torquing/Potential Conductor Damage, Wire Strip Length: 1-5/32 IN, Dimension B: 1.16 IN, Dimension T: 0.18 IN, Dimension K: 0.39 IN, Dimension N: 0.91 IN, Set Screw Type: Hex Head, Tongue Width: 1.5 IN, Length: 49 IN, Installation Torque: 375 IN-LB, Stud/bolt Hole Size: 3/8 IN

## Product Details

### General

Application	For Joining A Wide Range Of Copper Cable To Equipment Pads Or Bar And Offset Tongue, Non-Plated
Connector Type	Terminal
Hardware Type	5/8 UNF Socket/HexScrew
Installation Torque Recommended in-lb	275
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Number of Screws	1
Physical Attribute - Screw Type	Allen
Plated	N
Plating Type	Unplated
Sub Brand	SCRULUG
Trade Name	SCRULUG™
Type	Bolted Lugs & Terminals
UPC	781810351437

### Dimensions

Dimension - B Length fraction	1-13/32 in
Dimension - B Length inch	1.42 in
Dimension - Hole Size inch	0.39 in
Dimension - Hole Size mm	10 mm
Dimension - L Length Overall mm	104 mm
Dimension - Length Overall inch	4.09 in
Dimension - N inch	0.91 in
Dimension - Pad Width inch	1.50 in
Dimension - Screw Size inch	5/8

Dimension - Strip Length inch	1-5/32
Dimension - Stud Size inch	3/8

### Conductor Related

Conductor - Copper Str Size	1/0 ;2/0 AWG;3/0 AWG;4/0 AWG;250 kcmil;300 kcmil;350 kcmil;400 kcmil;450 kcmil;500 kcmil
Conductor - Copper Str Size Range	1/0 -500 kcmil
Conductor Type	CU C Str-Size

### Certifications and Compliance

Certification - CSA Approved	No
Certification - ETL	No
Certification - UL Listed Direct Burial	No
Certification - UL Recognized	No
Certification - cULus	Yes
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	No

### Logistics

Carton Quantity	18 EA
Minimum Pack Quantity	1

**For further technical assistance, please contact us**

**BURNDY Headquarters**  
 47 East Industrial Park Drive  
 Manchester, New Hampshire 03109

**Customer Service Hours:**  
 8 AM - 8 PM Eastern Monday-Friday  
 Emergency Service 24-hours/365 Days  
 Phone: 1-800-346-4175  
 1-603-647-5299 (International)