

TP1610LF

by Burndy
Catalog ID: TP1610LF

Prop 65 Notice

Copper Vinylug, .85 in L, .320 in W, Tin Plated, 600 Volts Max., 105 Deg C Max, Stud size: #8- #10.

Features: Type TP-LF Is A Variation Of The Type TP Design And Employs A Locking Fork Tongue For Fast Installation And Security, 600 V Maximum, 105 DEG C Maximum, Locking Fork Tongue Design: Allows Fast Installation-Screw Only Has To Be Loosened For Termination, Internal Configuration Of The Fork: Prevents The Terminal From Coming Off The Screw Without Applying A Pulling Force, Locking Fork Is Made From A Copper Alloy: Permits Many Installations While Maintaining Proper Spring Retention Of Forks, Temperature Rating: 105 DEG C Maximum, Bulk Catalog Number: BA16EL10, Tape Mounted Catalog Number: BA16EL10M, Insulation Diameter (maximum): 0.145 IN, Installation Tool: Plier Type: Y10-22 Tool, Ratchet: MR8-89-1, MR15 Tool, Wire Strip Length: 13/64 IN, Color Code: Red, Wire Insulation Grip: No, Finish: Electro-Tin Plated



Product Details

General

Application	For Fast Installation And Security
Color Code	Red
Connector Type	Terminal
Feature - Barrel Style	Shrouded
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Physical Attribute - Number of Holes	1
Physical Attribute - Tongue Type	Locking Fork
Plated	Y
Plating Type	Tin
Sub Brand	VINYLUG
Trade Name	VINYLUG™
Type	TP-LF, Locking
UPC	781810713600
UPC 12 Digit	7818107136000

Dimensions

Cable Insulation Diameter Maximum	0.145 in
Dimension - Hole Size fraction	15/79
Dimension - Hole Size inch	0.19 in
Dimension - L Length Overall mm	26 mm
Dimension - Length Overall inch	1.02 in
Dimension - Pad Width inch	0.36 in
Dimension - Strip Length inch	1/4 in

Dimension - Stud Size inch	#10
Dimension - Z inch	0.31 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor Range	#20 AWG to #22 AWG; 16 AWG to 18 AWG
Conductor Type	<ul style="list-style-type: none">• CU C Solid-Size• CU C Str-Size

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Carton Quantity	1200 EA
Minimum Pack Quantity	100

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)