



BS14

by Burndy
Catalog ID: BS14

Prop 65 Notice

Copper Splice, 16-14 AWG, 1" Splice Length, Vinyl Insulated, Tin Plated.

Features: The Type SP VINYLINK Is A PVC Insulated Seamless Butt Splice, Type SP VINYLINK Is Designed To Accommodate A Broad Range Of 600 Volt Cables, Manufactured From Seamless Electrolytic Copper Tubing: Provides Maximum Conductivity And Tensile Strength, In A High Quality Design With NO Seams To Split, Funnel Entry: Provides Easy Wire Insertion, Electro-Tin Plated: Provides Durable Long Lasting Resistance To Corrosion, Expanded Insulation Support: Lower Inventory Requirements, Red Wire Range Of 22-16: Lower Inventory Requirements, Vinyl Insulator: Economical Means Of Providing High Dielectric Values And Cable Insulation Support, Package: Bulk, Installation Tool: Non-Ratchet: Y10D, Y10-22 Tool, Ratchet: MR8G98, MR8-89-1, MR15 Tool, Conductor Type: Commercial/Aircraft Stranded Copper, Wire Strip Length: 1/4 IN, Insulation Support: Yes, Color Code: Blue

Product Details

General

Application	For Accommodating A Broad Range Of 600 Volt Cables
Color Code	Blue
Connector Type	Splice
Insulation	Y
Insulation Type	Vinyl
Material	Copper
Plated	Y
Plating Type	Tin
Sub Brand	VINYLINK
Temperature Rating	105
Trade Name	VINYLINK™
Type	BS
UPC	781810805688
UPC 12 Digit	7818108056888

Dimensions

Dimension - Diameter Max Size inch	0.18 in
Dimension - Length Overall inch	1.00 in
Dimension - Outside Diameter inch	0.18 in
Dimension - Strip Length inch	1/4 in

Electrical Ratings

Voltage - Maximum	600 V
-------------------	-------

Conductor Related

Conductor - Copper Solid Size Range	16 AWG-14 AWG
Conductor - Copper Str Size Range	16 AWG-14 AWG

Conductor Type	CU C Str-Size
----------------	---------------

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Industry Standard(s)	UL467
Standards - Industry Standards Met	UL467
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1000
-----------------------	------

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)