



YAV2CL2NTCFX

by Burndy
Catalog ID: YAV2CL2NTCFX

Prop 65 Notice

Copper Compression Lug, 2 Hole w/ Inspection Window, 2 Flex, 1/2" Stud, 1-3/4" Stud Hole Spacing, Short Barrel, Tin Plated.

Features: UL Listed 90 DEG C, 600 V - 35 KV, 45 DEG And 90 DEG Angles Are Available.

Product Details

General

Application	For Flex Conductors
Color Code	Brown
Connector Type	Terminal
Die Index	10
Feature - Barrel Style	Chamfered
Feature - Barrel Type	Standard
Material	Copper
Physical Attribute - Number of Holes	2
Plated	Y
Plating Type	Tin - Electro Plated
Sub Brand	HYLUG
Trade Name	HYLUG™
Type	Standard Barrel, Tin Plated
UPC	781810044582
UPC 12 Digit	7818100445822

Dimensions

Dimension - B Length fraction	5/8 in
Dimension - B Length inch	0.63 in
Dimension - Bolt Hole Size inch	0.52 in
Dimension - Hole Size inch	0.56 in
Dimension - Hole Size mm	14 mm
Dimension - L Length Overall mm	103 mm
Dimension - Length Overall inch	4.07 in
Dimension - N inch	0.62 in
Dimension - Outside Diameter inch	0.46 in
Dimension - Pad Width inch	0.83 in
Dimension - Strip Length inch	11/16
Dimension - Z inch	0.65 in
Physical Attribute - Tongue Angle	Straight

Electrical Ratings

Rating - KVA	35 kV
Rating - Minimum Voltage	600
Voltage - Maximum	35000

Conductor Related

Conductor - Copper DLO Size	3 (125/#24) DLO;2 (150/#24) DLO
Conductor - Copper Flex G Size	2 AWG
Conductor - Copper Flex H Size	2 AWG
Conductor - Copper Flex I Size	2 AWG
Conductor - Copper Flex K Size	2 AWG
Conductor - Copper Flex M Size	2 AWG
Conductor - Copper Solid Size	2 AWG
Conductor - Copper Str Navy Size	60 (37) Navy
Conductor - Copper Str Size	2 AWG
Conductor - CopperWeld Str Size	2 A AWG;2 F AWG;2 G AWG;2 J AWG;2 K AWG;2 N AWG;2 P AWG
Conductor - Material	Copper

Certifications and Compliance

Certification - CSA Approved	Yes
Certification - ETL	No
Certification - UL Recognized	No
Certification - cULus	No
Standards - RoHS Compliance Status	CM
UL Listed	Yes

Logistics

Minimum Pack Quantity	1
-----------------------	---

For further technical assistance, please contact us

BURNDY Headquarters
47 East Industrial Park Drive
Manchester, New Hampshire 03109

Customer Service Hours:
8 AM - 8 PM Eastern Monday-Friday
Emergency Service 24-hours/365 Days
Phone: 1-800-346-4175
1-603-647-5299 (International)