



Eaton XB IEC terminal block

XBUT25BU

UPC:782116894277

Dimensions:

- **Height:** 1.85 IN
- **Length:** .205 IN
- **Width:** X

Warranties:

- 1 year

Specifications:

- **Type:** IEC-XB Series
- **Amperage Rating:** 32A (IEC), 22A (EN), 28A (EN), 20A (UL)
- **Voltage Rating:** IEC 800V, EN 700V, UL 600V
- **Maximum Wire Size:** 12 AWG/2.5 mm²
- **Wire Size:** (3) #26-12 AWG
- **Color:** Blue

Supporting documents:

- [XB IEC TERMINAL BLOCKS](#)
- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [XBUT25 AutoCAD 2D Footprint \(mm\)](#)
- [XBUT25 2D Drawing Xchange](#)
- [XBUT25 AutoCAD 2D Footprint](#)
- [XBUT25 3D Inventor](#)
- [XBUT25 3D Model Xchange](#)
- [XBUT25 2D PDF](#)
- [XB IEC terminal blocks-versatility, quality, and reliability](#)
- [Eaton Specification Sheet - XBUT25BU](#)

Certifications:

- UL Listed
- CSA Certified

Product compliance: No Data

