
MANUAL CONTROLLER

7833MD | [Pass & Seymour](#)



FEATURES & BENEFITS

Three pole, Three Phase AC Manual Motor Controller 30 amp, 600 watts., Suitable as Motor Disconnect - 10KA @ 600VAC, 30A max Class J fuse.



- High Horsepower rating of 20HP
- Gull-wing shaped brass terminal pressure clamps
- Constructed of glass-reinforced thermoplastic
- UL508 and cULus Listing of individual device and assembled device within enclosure
- Heavy-duty zinc-plated steel strap, two brass rivets secure strap to housing
- External screw-pressure-plate back and side wire terminal screws unstaked for use with ring terminals
- For covering patents, see www.legrand.us/patents.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

SPECIFICATIONS

GENERAL INFO

Number Of Poles: 3

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: C22.23 14

CSA Standard: Yes

UL Listing No: 508

UL Standard: Yes

UN SPSC: 39121512

DIMENSIONS

Depth (US): 1.80"

Height (US): 5.75"

Width (US): 4.50"

TECHNICAL INFORMATION

Amps: 30A

Volts: 600VAC

Watts: 600

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

