

CNY LED LED Canopy/Ceiling Luminaire







Catalog Numbei Notes

Specifications

Width:	CNY LED P1/P2 10"	CNY LED P3/P4 14"
Height:	4.5"	6"
Depth:	10"	14"
Weight:	6.5lbs	13lbs

Introduction

Туре

The CNY LED canopy luminaires are energy efficient and budget friendly, perfect for replacing up to 400W metal halide luminaires while saving up to 80% energy costs. Quick mount mechanism significantly reduces the installation time. CNY LED luminaires are DLC Premium listed and deliver quick payback!

With an expected service life of more than 10 years, the CNY LED eliminates frequent lamp and ballast replacements associated with traditional technologies.

Ordering Information

EXAMPLE: CNY LED P1 50K MVOLT DDB

CNY LED				
Series	Performance Package	Color Temperature ¹	Voltage	Finish
CNY LED	P1 4,500 lumens P2 6,600 lumens P3 11,100 lumens P4 14,000 lumens	40K 4000K 50K 5000K	MVOLT ² 120-277V	DDB Dark bronze WH ³ White

Accessories

ed and shipped separately

CNYBCP 14 Inch x 14 Inch Beauty Cover Plate

NOTES

- 1. Correlated color temperature (CCT) shown is nominal per ANSI C78, 377-2008.
- 2. MVOLT driver operates on any line voltage from 120-277V (50/60 Hz).
- 3. Available with P1 only.

FEATURES & SPECIFICATIONS

INTENDED USE

CNY LED luminaires are ideal, energy-efficient replacements for up to 400W MH canopy or ceiling luminaires. The CNY LED provides years of maintenance-free illumination for schools, malls, offices, parking areas, covered walkways and loading docks.

Cast-aluminum, corrosion-resistant housing with polyester powder paint for lasting durability. Castings are sealed with a one-piece gasket. Rated for outdoor installations. -40°C minimum ambient. Frosted lens is designed for uniform light distribution.

Includes an MVOLT (120-277V) driver. LEDs maintain 70% of light output at 50,000 or more hours of service life (L70/50,000 hours).

Mounts to a recessed junction box or surface mount with three conduit entry points. Can be pendant mounted with 34 NPT pendant stem provided by others. Quick mount mechanism significantly reduces installation time - no need to open the luminaire for installation.

LISTINGS

UL Listed to U.S. and Canadian safety standards for wet locations. Tested in accordance with IESNA LM-79 and LM-80 standards DesignLights Consortium® (DLC) Premium qualified product. Not all versions of this product may be DLC Premium qualified or DLC qualified. Please check the DLC Qualified Products List at www.designlights.org/QPL to confirm which versions are qualified.

Five-year limited warranty. Complete warranty terms located at:

Note: Actual performance may differ as a result of end-user environment and application. All values are design or typical values, measured under laboratory conditions at $25\,^{\circ}$ C. Specifications subject to change without notice.





Photometric Diagrams


Full photometric data report available within 2 weeks from request. Contact Acuity Tech Support.














Performance Data

Performance Package	Lumens	Input Power	Lumens Per Watt			
CNY LED P1	4,500	35W	127			
CNY LED P2	6,600	52W	128			
CNY LED P3	11,000	86W	128			
CNY LED P4	13,900	109W	128			

Line Art

