



High Output T12

F96T12/DX ALTO 15PK

Philips T12 fluorescent lamps provide high performance in a wide range of sizes, shapes, and types.

Product data

General Information	
Cap-Base	FA8 [FA8]
Life 3-Hr Start [Hrs]	12000 h
Features	ALTO® (ALTO)
Light Technical	
Color Code	57
Luminous Flux (Nom)	4775 lm
Color Designation	Daylight Deluxe
Design Mean Lumens	4200 lm
Correlated Color Temperature (Nom)	6500 K
Color Rendering Index (Nom)	90
Operating and Electrical	
Power (Rated) (Nom)	75 W
Mechanical and Housing	
Cap-Base Information	Green Base


Nominal Length (Inch)	96
Approval and Application	
Energy Saving Product	Not Applicable
Mercury (Hg) Content (Nom)	6.8 mg
Product Data	
Order product name	F96T12/DX ALTO 15PK
EAN/UPC - Product	046677372828
Order code	372821
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	15
Material Nr. (12NC)	927895005711
Net Weight (Piece)	0.001 kg

High Output T12

Dimensional drawing

Product

TL F96T12/DX 75W ALTO



F96T12 75W/57 ALTO

