



NUVO SERIES TWO 6.5" DVC IN-CEILING SPEAKERS

NV-2IC6-DVC |

FEATURES & BENEFITS

The NUVO In-Ceiling speakers are designed to perform and look great. These speakers are specifically designed for smaller rooms, or rooms where a pair of speakers typically wouldn't be found. The NV-2IC6-DVC has two silk dome tweeters and a 6.5" dual voice coil poly woofer. This speaker offer a super clean look, and is finished beautifully with their completely rimless, magnetic grill. They offer quick and secure installation by utilizing three dog legs, instead of the usual four, and includes a unique tweeter bridge that maximizes sound quality, looks great, and serves as a handle to hold the speaker by during installation.



- 8 ohm rated
- Single Stereo Speaker
- Three dog leg design for easy installation
- Magnetic rimless and paintable grill
- Unique tweeter bridge that also doubles as an installation handle
- Lifetime Warranty

SPECIFICATIONS

Wattage: 50W rms
Maximum Wattage: 100W Peak
Woofer Diameter: 6.5" (165mm)
Woofer Composition: Poly
Surround Material: Rubber
Number of Woofers: 2
Tweeter Size: 0.5" diameter (13mm)
Tweeter Composition: Silk Dome
Number of Tweeters: 1
Decibels: 86 dB
Sensitivity: 86 dB (1 watt/meter)

Impedance: 8Ω
Frequency Response: 55 Hz - 20 KHz (+/- 3 dB)
Cutoff Frequency: 2.7 KHz

GENERAL INFO

Color: White
Type: Indoor, In-Ceiling, Round
Special Features: Magnetic thin bezel, poly woofer, UFLC soft dome tweeter, steel powder coated grill

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

DIMENSIONS

Depth (Metric): 99mm
Depth (US): 3.90"
Height (Metric): 230mm
Height (US): 9.06"
Length (Metric): 97mm
Length (US): 3.82"
Width (Metric): 230mm
Width (US): 9.06"

TECHNICAL INFORMATION

Frequency Response: 55 Hz - 20 KHz (+/- 3 dB)
Material: ABS frames and stamped metal baskets
Mounting: Cutout Round: 8.07" (205mm)
NEMA Rating: 5WD Wiring Devices, Building Systems
Speaker Impedance Load: 8Ω
Tweeter Type: Silk Dome
Watts: 50W RMS
Woofer Type: Poly