
QUICK CONNECT RJ25 6-POSITION, 6-CONDUCTOR TELEPHONE KEYSTONE INSERT, GRAY

WP3473-GY | [On-Q](#)

FEATURES & BENEFITS

Part of the Quick Connect family of products, this RJ25 keystone insert supports up to three telephone lines and accepts an RJ45 plug without damage.



- Supports up to 3 telephone lines
- 50 microinches of gold on contacts
- QuickConnect termination for reduced installation time
- FCC Part 68 compliant

SPECIFICATIONS

GENERAL INFO

Color: Gray
Performance Category: Cat 3
UL Standards Tested: UL Flammability Rating: UL 94V-0
Termination: 6P6C
Connection Type: RJ25 Female
Type: Keystone Insert
Input Plug Type: RJ25
Special Features: QuickConnect

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UL Listing No: ANSI/UL 1863
UL Standard: Yes

DIMENSIONS

Height (US): 6"

Length (US): 0.7"
Width (US): 4"

TECHNICAL INFORMATION

Jack Connectors: RJ25

Material: High Impact Flame Retardant Plastic

Operating Temperature (Celsius): -10° C to 60° C

Storage Temperature: -40° C to 70° C

Supported Standards: CSA, cULus, RoHS

Receptacle Type: RJ25 Female

Equipment Type: Quick Connect RJ25 6-Position, 6-Conductor Telephone Keystone Insert