

---

## 4-PORT SURFACE BOX

WP3504-LA | [On-Q](#)

---

### FEATURES & BENEFITS

For installations where mounting keystone inserts in-wall is not an option, this 4-port keystone surface mount box supports any On-Q keystone insert.



- Surface mount box supports up to 4 keystone inserts
- Easily mounts to walls using double-sided tape or screws

---

### SPECIFICATIONS

#### GENERAL INFO

Color: Light Almond  
Performance Category: Cat 3  
UL Standards Tested: UL Flammability Rating: UL 94V-0  
Termination: 6P6C  
Connection Type: RJ25 Female  
Type: Surface Mount Box  
Input Plug Type: RJ25  
Special Features: QuickConnect

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

#### DIMENSIONS

Height (US): 9"  
Length (US): 1.2"  
Width (US): 5.875"

#### TECHNICAL INFORMATION

Jack Connectors: RJ25

Material: High Impact Flame Retardant Plastic

Operating Temperature (Celsius): -10° C to 60° C

Storage Temperature: -40° C to 70° C

Receptacle Type: RJ25 Female

Number Of Receptacles: 4

Equipment Type: Quick Connect RJ25 6-Position, 6-Conductor Telephone Keystone Insert