
18GBPS PREMIUM CERTIFIED SLIM LINE HDMI CABLES WITH ETHERNET, 2 METER

AC3MP2-WH |



FEATURES & BENEFITS

The Premium Certified Slim Line HDMI Cables with Ethernet have undergone rigorous testing to verify that they comply with the HDMI 2.0b specification and can deliver 4K UltraHD, HDR, and other advanced features. Each cable bears the Premium HDMI Certification label to guarantee authenticity.

The Slim Line Cable offers incredible flexibility when patching between rack mounted devices or around tight corners. The slender form saves space behind equipment for easier cable management and cleaner installations.

- Premium HDMI Certified to comply with the HDMI 2.0b specification and marked with the anti-counterfeit label to ensure authenticity
- Supports: 18.2Gbps bandwidth, UltraHD - 4K@60Hz 4:4:4, High Dynamic Range (HDR), Deep Color, ARC, Ethernet
- Available in lengths from 1 to 2 meters
- Offers incredible flexibility when patching between rack mounted devices or around tight corners
- Smaller form factor saves space behind equipment for easier cable management
- Rated: CL3
- Ideal applications: rack-mount patching, short-length plat panel connections, desktop

SPECIFICATIONS

GENERAL INFO

Color: White

DIMENSIONS

Length (Metric): 2m

CORD INFORMATION

Connector Type End One: Type A, 19PIN Male

Connector Type End Two: Type A, 19PIN Male

Cord Length Metric: 2m

TECHNICAL INFORMATION

Humidity: 10 ~ 90%, Relative Humidity (non-condensing)

Material: PVC Molding Housin

Operating Temperature (Celsius): 0° ~ 43°C

Supported Standards: UL, RoHS

Wire Gauge: 32 AWG