



Centium T8 Instant Start

CENTIUM ELE BALLAST (2) F32T8 120-277V

Reliable and energy efficient Philips Advance's Centium commercial grade specifications, plus added benefits of lamp striation reduction technology.

Product data

General Information				
Lamp Type	F32T8			
Number of Lamps	1/2 piece/unit			
Ballast Type	Electronic Fluorescent			
Base Model	ICN2P32N			
Suitable For Outdoor Use	Yes			
Automatic Restart	Yes			
Operating and Electrical				
Input Voltage	120 to 277 V			
Input Frequency	50 to 60 Hz			
Total Harmonic Distortion USA	10 %			
Ignition Method	Instant Start			
Crestfactor (Nom)	1.7			
Ignition Time (Nom)	0.1 s			
Ballast Factor (Nom)	0.89			
Power Factor (Nom)	0.98			
Input Current (Max)	0.49 A			
Input Current (Min)	0.22 A			
Input Power (Nom)	56-56 W			
Rated Lamp Power	32 W			

No terminals		
No terminals		
0.50/0.375 mm		
Parallel		
See data sheet		
18AWG mm		
Solid		
Yes		
Yes		
Yes		
ES = 6' / Standard = 20'		
ES = 6' / Standard = 20'		
g ES = 6' / Standard = 20'		
No connector		
70 ℃		
Metal		
N		


Datasheet, 2019, March 22 data subject to change

Centium T8 Instant Start

Housing Dimensions	9.5" × 1.3" × 1.0"	
Approval and Application		
EMC Immunity Standard	FCC Non-Consumer	
Approval Marks	CSA certificate UL certificate CEC Listing	
	CEE Rated CSA E NEMA Premium NOM	
	certificate RoHS Compliant	
Hum And Noise Level	А	
UL Recognized	No	
Product Data		
Full product code	578108706913430	

Order product name	CENTIUM ELE BALLAST (2) F32T8 120-277V
EAN/UPC - Product	781087069127
Order code	913710842702
Numerator - Quantity Per Pack	1
Numerator - Packs per outer box	30
Material Nr. (12NC)	913710842702
Net Weight (Piece)	305.000 g

Dimensional drawing



Product	A1	A2	B1	C1
CENTIUM ELE BALLAST (2) F32T8 120-277V	9.50 in	8.90 in	1.30 in	1.00 in



© 2019 Signify Holding All rights reserved. Signify does not give any representation or warranty as to the accuracy or completeness of the information included herein and shall not be liable for any action in reliance thereon. The information presented in this document is not intended as any commercial offer and does not form part of any quotation or contract, unless otherwise agreed by Signify. All trademarks are owned by Signify Holding or their respective owners.