

Eaton M22 modular pushbutton

M22-L-Y-230W

UPC:786685278667

Dimensions:

- **Height:** 2.22 IN
- **Length:** 1.46 IN
- **Width:** 1.18 IN

Weight:.085 LB

Warranties:

- Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Specifications:

- **Type:** Complete Indicating Light
- **Actuator:** Flush
- **Environmental Rating:** IP67, IP69K, NEMA 4X, 13
- **Size:** 22.5 mm
- **Illumination:** Illuminated
- **Lens Color:** Yellow
- **Light Color:** White
- **Operating Cycles:** 100,000 Hours of operation
- **Series:** M22
- **Voltage Rating:** 85-264 Vac/dc

Supporting documents:

- [Eatons Volume 7-Logic Control, Operator Interface and Connectivity Solutions](#)
- [M22-L AutoCAD 2D Footprint \(mm\)](#)
- [M22-L 3D Inventor](#)
- [M22-L 2D PDF](#)
- [M22-L 3D Model Xchange](#)
- [M22-L AutoCAD 2D Footprint](#)
- [M22-L 2D Drawing Xchange](#)
- [M22 Operators and Accessories](#)



- [M22 Pilot Devices](#)
- [Global Data Sheet - M22-L-Y-230W](#)
- [Eaton Specification Sheet - M22-L-Y-230W](#)

Certifications:

- CSA Certified
- CCC Marked
- Lloyd's Register Certified

Product compliance:

- GoST-R
- CE Marked
- Bureau Veritas