



S9384

6.5MR16/LED/40°/40K/120V/GU10
 6.5 watt; LED MR16 LED; 4000K; 40° beam spread; GU10 base; 120 volts

Features

- Solid State LED lighting
- High Efficacy
- Long life
- Dimmable
- UL approved for totally enclosed fixtures



S9384

Item Number	UPC	Voltage	Watts	Incandescent Equivalent	Power Factor	Lamp Shape	Base
S9384	045923093845	120	6.5	50W	0.92	MR16	GU10

Lamp Code	Dimmable/Non-Dimmable	Suggested Dimmers	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours	Kelvin Temp
6.5MR16/LED/40°/40K/120V/GU10	Dimmable	Compatible dimmers for S9384	2-3/16"	2.00"	500	25000	4000

Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	CEC Status	RoHS Compliant
Cool White	80	40	-25C (-13F) to a maximum of +45C (+113F)	48/12	Box	Lawful for sale in California	Yes
UL or ETL Listed			Warranty				
Yes			5 Year Limited - 10 hour use per day				



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027

