


Project Name

Location

Prepared By



Notes

[www] 03-22-2021 04:50:59

General

Status	Active
Type	Track Head
Wattage	12
Finish	Black
Beam Angle	36
CCT (Kelvin)	3000
Temperature	Warm White
ANSI Base	LED Module
Indoor or Outdoor Fixture	Indoor

Specifications

CRI	90
Lumen Output	1000
Rated Hours	30000
Voltage	120V
Dimmable	Yes - Dimmable
Weight (lb.)	1.05

Dimensions

Height (in.)	2.81
Width (in.)	2.81
Length (in.)	3.63
Extension (in.)	5.5

Compliance

Safety Listing	cETLus
Location Rating	Dry
UL Application	Track
Energy Star	No
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes

Additional Information

Warranty	3 Year Limited - Fixtures
----------	---------------------------