

Project Name

Location

Prepared By



SATCO S9030

5.5A15/LED/2700K/120V

Notes

[www] 03-22-2021 04:50:58

General

Status	Active
Watts	5.5
Incandescent Equivalent	40
Volts	120V
Shape	A15
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	2700
Temperature	Warm White
CRI	83
Lumens	450
Beam Spread	230
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	60 Hz
Power Factor	0.79
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	3.47
MOD	1.88
Housing Color	White

Additional Information

Rated For Enclosed Fixture	Yes
Installation Notes	Not for use in ovens
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2288340
California Status	Non-Compliant
California Compliant Substitute	S8572
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp