


Project Name

Location

Prepared By



Notes

[www] 03-15-2021 00:27:55

**General**

Status	Active
Type	Track Kit
Wattage	36
Finish	White
Beam Angle	36
CCT (Kelvin)	3000
Temperature	Warm White
Base	Integrated LED
ANSI Base	Integrated LED
Indoor or Outdoor Fixture	Indoor

**Specifications**

CRI	90
Lumen Output	3000
Rated Hours	30000
Voltage	120V
Dimmable	Yes - Dimmable

**Dimensions**

Height (in.)	2.81
Width (in.)	2.81
Length (in.)	3.63
Extension (in.)	5.5
Weight (lb.)	5.27

**Compliance**

Safety Listing	cETLus
Location Rating	Dry
UL Application	Track
Energy Star	No
California Status	California T24 Compliant
California Prop 65	Lead
RoHS Compliant	Yes

**Additional Information**

Includes	Four foot track
Warranty	3 Year Limited - Fixtures