

Project Name

Location

Prepared By



SATCO S8916

8.5A19/LED/40K /120-277V

Notes

[www] 11-09-2020 01:16:25

General

Status	Active
Watts	8.5
Incandescent Equivalent	60
Volts	120V-277V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	4000
Temperature	Cool White
CRI	80
Lumens	800
Beam Spread	220
Dimmable	Non-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	50/60 Hz
Power Factor	0.91/0.7
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	4.31
MOD	2.38
Housing Color	White

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Non-Compliant
RoHS Compliant	Yes
SDS Sheet	LED_Lamp