SATCO' NUVO

Project Name

Location

Prepared By



SATCO S8640 8MR16/LED/40'/27K/90CRI/12V

Notes

General Status Active Watts 8 75 Incandescent Equivalent Volts 12V Shape MR16 Base Bi Pin GU5.3 ANSI Base GU5.3 Finish Clear CCT (Kelvin) 2700 Temperature Warm White CRI 90 Lumens 490 Beam Spread 40 Dimmable Yes - Dimmable Hours Rated 25000 Lamp Type MR Technology LED Electrical CBCP 1220 1175 Candlepower Power Factor 0.9 -25C (-13F) to a maximum of +45C **Operating Temperature** (+113F) Physical MOL 1.88 MOD 2 Lensed Lensed Lamp Housing Color Gray Additional Information Rated For Enclosed Fixture Yes Warranty 5 Year Limited - 10 hr per day Compliance cULus Safety Listing Location Rating Damp Energy Star Yes ESID-2305845 ES Unique ID California Status California T24 Compliant Nevada Status Lawful for sale in Nevada **RoHS** Compliant Yes SDS Sheet LED_Lamp

For More Information Visit: <u>https://www.satco.com/</u>

