

Project Name

Location

Prepared By



SATCO S29818

15A19/LED/5000K/1600L/120V/D

Notes

[www] 03-22-2021 04:50:55

General

Status	Active
Watts	15
Incandescent Equivalent	100
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	85
Lumens	1600
Beam Spread	220
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Power Factor	0.94
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	4.63
MOD	2.38

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2307668
California Status	Non-Compliant
California Compliant Substitute	S8487
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp