

Project Name

Location

Prepared By



SATCO S29830

6A19/OMNI/220/LED/27K

Notes

[www] 03-22-2021 04:50:59

General

Status	Active
Watts	6
Incandescent Equivalent	40
Volts	120V
Shape	A19
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	2700
Temperature	Warm White
CRI	83
Lumens	480
Beam Spread	220
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Power Factor	0.98
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	4.31
MOD	2.38
Housing Color	White
Weight (lb.)	0.09

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - 10 hr per day

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2307966
California Status	Non-Compliant
California Compliant Substitute	S9703
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp