SATCO" NUVO

Project Name



SATCO S29838

9.8A19/OMNI/220/LED/40K

Notes

General Status Active Watts 9.8 60 Incandescent Equivalent Volts 120V Shape A19 Base Medium ANSI Base E26 Finish Frosted White CCT (Kelvin) 4000 Temperature Cool White CRI 86 Lumens 800 Beam Spread 220 Dimmable Yes - Dimmable Hours Rated 25000 Lamp Type Type A Technology LED Electrical Power Factor 0.98 -25C (-13F) to a maximum of +45C **Operating Temperature** (+113F) Physical MOL 4.31 MOD 2.38 Weight (lb.) 0.08 Additional Information Rated For Enclosed Fixture Yes Warranty 5 Year Limited - 10 hr per day Compliance Safety Listing cULus Location Rating Damp Energy Star Yes ES Unique ID ESID-2307831 California Status Non-Compliant California Compliant Substitute S8480 Nevada Status Lawful for sale in Nevada **RoHS** Compliant Yes SDS Sheet LED_Lamp

For More Information Visit: https://www.satco.com/

