

Project Name

Location

Prepared By



SATCO S8735

20WA21/LED/27K/120V/DIM

Notes

[www] 03-22-2021 04:50:55

General

| | |
|-------------------------|----------------|
| Status | Active |
| Watts | 20 |
| Incandescent Equivalent | 125 |
| Volts | 120V |
| Shape | A21 |
| Base | Medium |
| ANSI Base | E26 |
| Finish | Frosted White |
| CCT (Kelvin) | 2700 |
| Temperature | Warm White |
| CRI | 84 |
| Lumens | 2350 |
| Beam Spread | 280 |
| Dimmable | Yes - Dimmable |
| Hours Rated | 25000 |
| Lamp Type | Type A |
| Technology | LED |

Electrical

| | |
|-----------------------|--|
| Candlepower | 185 |
| Power Factor | >0.9 |
| Operating Temperature | -25C (-13F) to a maximum of +45C (+113F) |

Physical

| | |
|---------------|-------|
| MOL | 5 |
| MOD | 2.63 |
| Housing Color | White |

Additional Information

| | |
|----------------------------|-------------------------|
| Rated For Enclosed Fixture | Yes |
| Warranty | 5 Year Limited - Hi-Pro |

Compliance

| | |
|-------------------|---------------------------|
| Safety Listing | cULus |
| Location Rating | Damp |
| Energy Star | Yes |
| ES Unique ID | ESID-2321957 |
| California Status | Non-Compliant |
| Nevada Status | Lawful for sale in Nevada |
| RoHS Compliant | Yes |
| SDS Sheet | LED_Lamp |