

Project Name

Location

Prepared By



SATCO S8736

20WA21/LED/5K/120V/DIM

Notes

[www] 03-15-2021 00:27:54

General

Status	Active
Watts	20
Incandescent Equivalent	150
Volts	120V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	83
Lumens	2860
Beam Spread	280
Dimmable	Yes - Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Candlepower	204
Power Factor	>0.9
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	5
MOD	2.63
Housing Color	White

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2321958
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp