

Project Name

Location

Prepared By



SATCO S8738

20WA21/LED/5K/120-277V

Notes

[www] 03-22-2021 04:50:55

General

Status	Active
Watts	20
Incandescent Equivalent	150
Volts	120V-277V
Shape	A21
Base	Medium
ANSI Base	E26
Finish	Frosted White
CCT (Kelvin)	5000
Temperature	Natural Light
CRI	83
Lumens	2910
Beam Spread	280
Dimmable	Non-Dimmable
Hours Rated	25000
Lamp Type	Type A
Technology	LED

Electrical

Operating Frequency	50/60 Hz
Candlepower	209
Power Factor	>0.9
Operating Temperature	-25C (-13F) to a maximum of +45C (+113F)

Physical

MOL	5
MOD	2.63
Housing Color	White

Additional Information

Rated For Enclosed Fixture	Yes
Warranty	5 Year Limited - Hi-Pro

Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	Yes
ES Unique ID	ESID-2321961
California Status	Lawful for sale in California
Nevada Status	Lawful for sale in Nevada
RoHS Compliant	Yes
SDS Sheet	LED_Lamp