

Part numbers

Molded Case Circuit Breakers

Tmax T7 1200 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

Iu (40°C) = 1200 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current	Part number		
	In	S (25kA)	H (50kA)	L (65kA)
PR231/P-LS/I	1200 A (400...1200 A)	T7S1200BW	T7H1200BW	T7L1200BW
PR232/P-LSI	1200 A (400...1200 A)	T7S1200CW	T7H1200CW	T7L1200CW
PR331/P-LSIG	1200 A (400...1200 A)	T7S1200EW	T7H1200EW	T7L1200EW
PR332/P-LI	1200 A (400...1200 A)	T7S1200PW	T7H1200PW	T7L1200PW
PR332/P/LSI	1200 A (400...1200 A)	T7S1200RW	T7H1200RW	T7L1200RW
PR332/P-LSIG	1200 A (400...1200 A)	T7S1200SW	T7H1200SW	T7L1200SW

Tmax T7 1200 A - FIXED (F) 3 poles - 100% rated - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

Iu (40°C) = 1200 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current	Part number		
	In	SQ (25kA)	HQ (50kA)	LQ (65kA)
PR231/P-LS/I	1200 A (400...1200 A)	T7SQ1200BW	T7HQ1200BW	T7LQ1200BW
PR232/P-LSI	1200 A (400...1200 A)	T7SQ1200CW	T7HQ1200CW	T7LQ1200CW
PR331/P-LSIG	1200 A (400...1200 A)	T7SQ1200EW	T7HQ1200EW	T7LQ1200EW
PR332/P-LI	1200 A (400...1200 A)	T7SQ1200PW	T7HQ1200PW	T7LQ1200PW
PR332/P/LSI	1200 A (400...1200 A)	T7SQ1200RW	T7HQ1200RW	T7LQ1200RW
PR332/P-LSIG	1200 A (400...1200 A)	T7SQ1200SW	T7HQ1200SW	T7LQ1200SW

Tmax T7 1200 A - FIXED (F) 4 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

Iu (40°C) = 1200 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current	Part number		
	In	S (25kA)	H (50kA)	L (65kA)
PR231/P-LS/I	1200 A (400...1200 A)	T7S1200BW-4	T7H1200BW-4	T7L1200BW-4
PR232/P-LSI	1200 A (400...1200 A)	T7S1200CW-4	T7H1200CW-4	T7L1200CW-4
PR331/P-LSIG	1200 A (400...1200 A)	T7S1200EW-4	T7H1200EW-4	T7L1200EW-4
PR332/P-LI	1200 A (400...1200 A)	T7S1200PW-4	T7H1200PW-4	T7L1200PW-4
PR332/P/LSI	1200 A (400...1200 A)	T7S1200RW-4	T7H1200RW-4	T7L1200RW-4
PR332/P-LSIG	1200 A (400...1200 A)	T7S1200SW-4	T7H1200SW-4	T7L1200SW-4