

AF09-30-10-13

ABB contact for Canada [Print to Pdf..](#)

General Information

Extended Product Type:	AF09-30-10-13
Product ID:	1SBL137001R1310
EAN:	3471523110038
Catalog Description:	AF09-30-10-13 100-250V50/60HZ-DC Contactor
Long Description:	<p>AF09 contactors are used for controlling power circuits up to 690 V AC and 220 V DC. They are mainly used for controlling 3-phase motors, non-inductive or slightly inductive loads. AF... contactors include an electronic coil interface accepting a wide control voltage U_c min. ... U_c max. Only four coils cover control voltages between 24...500 V 50/60 Hz or 20...500 V DC. AF contactors can manage large control voltage variations. One coil can be used for different control voltages used worldwide without any coil change. AF contactors have built-in surge protection and do not require additional surge suppressors. The AF... series 1-stack 3-pole contactors are of the block type design. - Main poles and auxiliary contact blocks: 3 main poles, 1 built-in auxiliary contact, front and side-mounted add-on auxiliary contact blocks (mechanically-linked auxiliary contacts compliant with Annex L of IEC 60947-5-1. N.C. mirror contacts compliant with Annex F of IEC 60947-4-1) - Control circuit: AC or DC operated - Accessories: a wide range of accessories is available.</p>



Categories

Products » Low Voltage Products and Systems » Control Products » Contactors » Block Contactors

Ordering

EAN:	3471523110038
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369085

Dimensions

Product Net Width:	45.0 mm
Product Net Depth:	77.0 mm
Product Net Height:	86.0 mm
Product Net Weight:	0.270 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	87 mm

Package Level 1 Length:	79 mm
Package Level 1 Height:	47 mm
Package Level 1 Gross Weight:	0.27000 kg
Package Level 1 EAN:	3471523110038
Package Level 2 Units:	54 piece
Package Level 3 Units:	1296 piece

Environmental

Ambient Air Temperature:	Close to Contactor for Storage -60...+80 °C Close to Contactor Fitted with Thermal O/L Relay -25...+60 °C Close to Contactor without Thermal O/L Relay -40...+70 °C
Maximum Operating Altitude Permissible:	3000 m
Resistance to Shock acc. to IEC 60068-2-27:	Closed, Shock Direction: B1 25 g Open, Shock Direction: B1 5 g Shock Direction: A 30 g Shock Direction: B2 15 g Shock Direction: C1 25 g Shock Direction: C2 25 g
Resistance to Vibrations acc. to IEC 60068-2-6:	5...300 Hz 4 g closed position / 2 g open position
RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2008 Q1

Technical

Rated Operational Power AC-3 (P_e):	(220 / 230 / 240V) 2.2 kW (380 / 400V) 4 kW (415V) 4 kW (440V) 4 kW (500V) 5.5 kW (690V) 5.5 kW
Rated Operational Current AC-1 (I_e):	(690V) 40°C 25 A (690V) 60°C 25 A (690V) 70°C 22 A
Number of Main Contacts NO:	3
Number of Main Contacts NC:	0
Number of Auxiliary Contacts NO:	1
Number of Auxiliary Contacts NC:	0
Rated Control Circuit Voltage (U_c):	50 Hz 100...250 V 60 Hz 100...250 V DC Operation 100...250 V
Terminal Type:	Screw Terminals

Technical UL/CSA

Tightening Torque UL/CSA:	Auxiliary Circuit 11 in·lb Control Circuit 11 in·lb Main Circuit 13 in·lb
----------------------------------	---

Certificates and Declarations (Document Number)

CB Certificate:	CB_SE_70855M1
CCC Certificate:	CCC_2010010304445624
cUL Certificate:	UL_20091124-E312527-7-1

Declaration of Conformity - CE:	1SBD250164C3000
DNV Certificate:	DNV_E12810
EAC Certificate:	EAC_RU C-FR ME77 B01010
GL Certificate:	GL_3786412HH
GOST Certificate:	GOST_POCCFR.ME77.B07175.pdf
LR Certificate:	LRS_1300087
RINA Certificate:	RINA_ELE084013XG
RoHS Information:	1SBD251013E1000

Classifications

E-nummer:	3210009
UNSPSC:	39121529
