

Part numbers

Molded Case Circuit Breakers

Tmax T7 1000 A - FIXED (F) 3 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

Iu (40°C) = 1000 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current	Part number		
	In	S (25kA)	H (50kA)	L (65kA)
PR231/P-LS/I	1000 A (400...1000 A)	T7S1000BW	T7H1000BW	T7L1000BW
PR232/P-LSI	1000 A (400...1000 A)	T7S1000CW	T7H1000CW	T7L1000CW
PR331/P-LSIG	1000 A (400...1000 A)	T7S1000EW	T7H1000EW	T7L1000EW
PR332/P-LI	1000 A (400...1000 A)	T7S1000PW	T7H1000PW	T7L1000PW
PR332/P-LSI	1000 A (400...1000 A)	T7S1000RW	T7H1000RW	T7L1000RW
PR332/P-LSIG	1000 A (400...1000 A)	T7S1000SW	T7H1000SW	T7L1000SW

Tmax T7 1000 A - FIXED (F) 3 poles - 100% rated - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

Iu (40°C) = 1000 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current	Part number		
	In	SQ (25kA)	HQ (50kA)	LQ (65kA)
PR231/P-LS/I	1000 A (400...1000 A)	T7SQ1000BW	T7HQ1000BW	T7LQ1000BW
PR232/P-LSI	1000 A (400...1000 A)	T7SQ1000CW	T7HQ1000CW	T7LQ1000CW
PR331/P-LSIG	1000 A (400...1000 A)	T7SQ1000EW	T7HQ1000EW	T7LQ1000EW
PR332/P-LI	1000 A (400...1000 A)	T7SQ1000PW	T7HQ1000PW	T7LQ1000PW
PR332/P-LSI	1000 A (400...1000 A)	T7SQ1000RW	T7HQ1000RW	T7LQ1000RW
PR332/P-LSIG	1000 A (400...1000 A)	T7SQ1000SW	T7HQ1000SW	T7LQ1000SW

Tmax T7 1000 A - FIXED (F) 4 poles - CSA C22.2 No 5 / UL489 listed (Discount DS-ST)

Iu (40°C) = 1000 A - Front terminals (F)

Electronic trip unit (AC only) - 600V AC	Nominal current	Part number		
	In	S (25kA)	H (50kA)	L (65kA)
PR231/P-LS/I	1000 A (400...1000 A)	T7S1000BW-4	T7H1000BW-4	T7L1000BW-4
PR232/P-LSI	1000 A (400...1000 A)	T7S1000CW-4	T7H1000CW-4	T7L1000CW-4
PR331/P-LSIG	1000 A (400...1000 A)	T7S1000EW-4	T7H1000EW-4	T7L1000EW-4
PR332/P-LI	1000 A (400...1000 A)	T7S1000PW-4	T7H1000PW-4	T7L1000PW-4
PR332/P-LSI	1000 A (400...1000 A)	T7S1000RW-4	T7H1000RW-4	T7L1000RW-4
PR332/P-LSIG	1000 A (400...1000 A)	T7S1000SW-4	T7H1000SW-4	T7L1000SW-4